

**Adjustable caliper pin wrench flat, Pin nominal \varnothing : 2,5mm****Order data**

Order number	628600 2,5
GTIN	4020772040499
Item class	63Q

Description**Version:**

Special steel, drive head ground, hardened and burnished; with fixed pins.

Application:

For twin hole nuts.

Note:

Pin \varnothing = pin nominal \varnothing - 0.1 mm. Tolerance zone h12.

Technical description

Pin nominal \varnothing	2.5 mm
Pin spacing adjustable a	7 - 40 mm
Type	758
Manufacturer's designation	758
Length L	115 mm
swan necked	no
flat	yes
adjustable for width	yes
Type of product	Pin spanner

