

**C-hook (pin) spanner with pin, for external nut Ø: 180/195mm****Order data**

Order number	628500 180/195
GTIN	4020772055042
Item class	63Q

Description**Version:**

Special steel, drive head ground, hardened and burnished.
Hook spanner with round pin to DIN 1810 B.

Application:

For DIN 1816 capstan nuts.

Technical description

Pin Ø	10 mm
overall length	470 mm
for external nut Ø	180 - 195 mm
Type	1810A
Manufacturer's designation	DIN 1810B
Type of product	C-hook (pin) spanners