

**Hinged pin wrench straight, largest \varnothing / pin nominal \varnothing : 200/10mm****Order data**

Order number	628800 200/10
GTIN	4020772041120
Item class	63Q

Description**Version:**

Special steel, drive head ground, annealed and burnished.

With fixed pins.

Application:

For twin hole nuts.

Note:

Pin \varnothing = pin nominal \varnothing - 0.1 mm; tolerance field h12.

Technical description

largest \varnothing	200 mm
Pin spacing adjustable a	125 - 200 mm
overall length	405 mm
Pin nominal \varnothing	10 mm
Type	764C
Manufacturer's designation	764
Type of product	Pin spanner