

**Hinged pin wrench straight, largest  $\varnothing$  / pin nominal  $\varnothing$ : 40/3mm****Order data**

Order number	628800 40/3
GTIN	4020772041038
Item class	63Q

**Description****Version:**

Special steel, drive head ground, annealed and burnished.

With fixed pins.

**Application:**

For twin hole nuts.

**Note:**

Pin  $\varnothing$  = pin nominal  $\varnothing$  - 0.1 mm; tolerance field h12.

**Technical description**

largest $\varnothing$	40 mm
Pin nominal $\varnothing$	3 mm
Pin spacing adjustable a	18 - 40 mm
overall length	150 mm
Type	764C
Manufacturer's designation	764
Type of product	Pin spanner