

**C-hook (pin) spanner with pin, for external nut Ø: 58/62mm****Order data**

Order number	628500 58/62
GTIN	4020772054960
Item class	63Q

**Description****Version:**

Special steel, drive head ground, hardened and burnished.  
Hook spanner with round pin to DIN 1810 B.

**Application:**

For DIN 1816 capstan nuts.

**Technical description**

overall length	240 mm
Pin Ø	5 mm
for external nut Ø	58 - 62 mm
Type	1810A
Manufacturer's designation	DIN 1810B
Type of product	C-hook (pin) spanners