

**Hinged pin wrench straight, largest \varnothing / pin nominal \varnothing : 40/4mm****Order data**

Order number	628800 40/4
GTIN	4020772041045
Item class	63Q

Description**Version:**

Special steel, drive head ground, annealed and burnished.

With fixed pins.

Application:

For twin hole nuts.

Note:

Pin \varnothing = pin nominal \varnothing - 0.1 mm; tolerance field h12.

Technical description

largest \varnothing	40 mm
Pin nominal \varnothing	4 mm
overall length	150 mm
Pin spacing adjustable a	18 - 40 mm
Type	764C
Manufacturer's designation	764
Type of product	Pin spanner