

**Nut spinner set with T-handle VDE insulated, Number of keys: 4****Order data**

Order number	622775 4
GTIN	4010995370923
Item class	63K

**Description****Version:**

Cleanly formed, deep hexagon spinner head with internal hole for screw threads that project beyond the nut. Impact-resistant plastic T-handle, blade of chrome vanadium steel, chrome-plated, with sprayed-on protective insulation.

**Insulated up to 1000 V, made to DIN EN IEC 60900 / VDE 0682-201.**

**Content:**

1 pc. each No. 622770: Size 8; 10; 13; 17

**Technical description**

Number of keys	4
Standard	DIN EN IEC 60900 / VDE 0682-201
Drive profile	Hexagon socket
Type of product	Socket spanner

**Accessories**

622770 10

Nut spinner with T-handleVDE insulated Width across flats  
10 mm

Nut spinner with T-handleVDE insulated Width across flats  
8 mm

622770 8

Nut spinner with T-handleVDE insulated Width across flats  
13 mm

622770 13

Nut spinner with T-handleVDE insulated Width across flats  
17 mm

622770 17