

**Hinged pin wrench straight, largest  $\varnothing$  / pin nominal  $\varnothing$ : 80/6mm****Order data**

Order number	628800 80/6
GTIN	4020772041076
Item class	63Q

**Description****Version:**

Special steel, drive head ground, annealed and burnished.

With fixed pins.

**Application:**

For twin hole nuts.

**Note:**

Pin  $\varnothing$  = pin nominal  $\varnothing$  - 0.1 mm; tolerance field h12.

**Technical description**

Pin nominal $\varnothing$	6 mm
Pin spacing adjustable a	40 - 80 mm
overall length	220 mm
largest $\varnothing$	80 mm
Type	764C
Manufacturer's designation	764
Type of product	Pin spanner