



Adjustable caliper pin wrench flat, Pin nominal \varnothing : 10mm



Order data

Order number	628600 10
GTIN	4020772040901
Item class	63Q

Description

Version:

Special steel, drive head ground, hardened and burnished; with fixed pins.

Application:

For twin hole nuts.

Note:

Pin \varnothing = pin nominal \varnothing - 0.1 mm. Tolerance zone h12.

Technical description

Pin spacing adjustable a	22 - 125 mm
Pin nominal \varnothing	10 mm
Type	758
Manufacturer's designation	758
Length L	260 mm
swan necked	no
flat	yes
adjustable for width	yes
Type of product	Pin spanner

