

**C-hook (pin) spanner with pin, for external nut Ø: 135/145mm****Order data**

Order number	628500 135/145
GTIN	4020772055028
Item class	63Q

Description**Version:**

Special steel, drive head ground, hardened and burnished.
Hook spanner with round pin to DIN 1810 B.

Application:

For DIN 1816 capstan nuts.

Technical description

overall length	385 mm
for external nut Ø	135 - 145 mm
Pin Ø	8 mm
Type	1810A
Manufacturer's designation	DIN 1810B
Type of product	C-hook (pin) spanners