



## Double open ended spanner, Jaw widths: 13X15 mm



### Order data

Order number	610700 13X15
GTIN	4045197158925
Item class	61A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance.

#### Standard:

**DIN 3110 / ISO 3318**

#### Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

Spanner length L: 190 mm

maximum jaw width b1: 33 mm

maximum jaw width b2: 35 mm

maximum jaw height h: 6 mm

### Technical description

maximum jaw width b2	35 mm
Width across flats 2	15 mm
maximum jaw height h	6 mm
Width across flats 1	13 mm
maximum jaw width b1	33 mm
Width across flats	metric
Spanner length L	190 mm
Standard	DIN 3110
Standard	ISO 3318

Jaw position 1	15 degrees
Jaw position 2	15 degrees
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner