



## Double open ended spanner, Jaw widths: 14X17mm



### Order data

Order number	610100 14X17
GTIN	4018754017867
Item class	63A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission.

#### Standard:

**DIN 3110 / ISO 3318**

#### Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

#### Note:

**PLEASE NOTE!**

An alternative from GARANT is also available for this product.

Recommended product number: 610600

### Technical description

maximum jaw height h	6 mm
maximum jaw width b1	33 mm
Width across flats 2	17 mm
Width across flats 1	14 mm
maximum jaw width b2	39 mm
Width across flats	metric
Spanner length L	205 mm
Standard	ISO 3318
Standard	DIN 3110

Jaw position 1	15 degrees
Jaw position 2	15 degrees
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner