

Garant**Double open ended spanner, Jaw widths: 14X15mm****Order data**

Order number	610700 14X15
GTIN	4045197158949
Item class	61A

Description**Version:**

Drop-forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

Technical description

Width across flats 2	15 mm
Width across flats 1	14 mm
maximum jaw width b1	33 mm
maximum jaw height h	6 mm
maximum jaw width b2	35 mm
Width across flats	metric
Spanner length L	190 mm
Standard	DIN 3110
Standard	ISO 3318
Jaw position 1	15 degrees
Jaw position 2	15 degrees

non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner