



Double open ended spanner, Jaw widths: 24X27mm



Order data

Order number	610100 24X27
GTIN	4018754018000
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 610600

Technical description

maximum jaw width b2	60 mm
maximum jaw height h	9 mm
Width across flats 1	24 mm
maximum jaw width b1	54 mm
Width across flats 2	27 mm
Width across flats	metric
Spanner length L	280 mm
Standard	ISO 3318
Standard	DIN 3110

Jaw position 1	15 degrees
Jaw position 2	15 degrees
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner