



Double open ended spanner, inch, Type: 15



Order data

Order number	610120 15
GTIN	4018754019816
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Width across flats $_1$: 11/16 in

Width across flats $_2$: 3/4 in

Spanner length L: 220 mm

maximum jaw width b1: 40 mm

maximum jaw width b2: 42 mm

maximum jaw height h: 6.7 mm

Technical description

maximum jaw width b1	40 mm
Width across flats $_1$	11/16 in
maximum jaw height h	6.7 mm
maximum jaw width b2	42 mm
Width across flats	imperial
Width across flats $_2$	3/4 in
Spanner length L	220 mm

Standard	ISO 3318
Standard	DIN 3110
Jaw position 1	15 °
Jaw position 2	15 °
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner