



Double open ended spanner, Jaw widths: 14X17 mm



Order data

Order number	610700 14X17
GTIN	4045197158956
Item class	61A

Description

Version:

Drop forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

Spanner length L: 205 mm

maximum jaw width b1: 33 mm

maximum jaw width b2: 39 mm

maximum jaw height h: 6 mm

Technical description

maximum jaw height h	6 mm
Width across flats 2	17 mm
maximum jaw width b1	33 mm
maximum jaw width b2	39 mm
Width across flats 1	14 mm
Width across flats	metric
Spanner length L	205 mm
Norm	DIN 3110
Norm	ISO 3318

Jaw position 1	15 degrees
Jaw position 2	15 degrees
non-sparking	no
both sides have the same width across flats	no