



## Double open ended spanner, inch, Type: 18



### Order data

Order number	610120 18
GTIN	4018754019830
Item class	63A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission.

#### Standard:

**DIN 3110 / ISO 3318**

#### Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Width across flats  $_1$ : 3/4 in

Width across flats  $_2$ : 7/8 in

Spanner length L: 235 mm

maximum jaw width b1: 42 mm

maximum jaw width b2: 49 mm

maximum jaw height h: 7.3 mm

### Technical description

maximum jaw width b1	42 mm
maximum jaw width b2	49 mm
maximum jaw height h	7.3 mm
Width across flats	imperial
Width across flats $_2$	7/8 in
Spanner length L	235 mm
Width across flats $_1$	3/4 in

Standard	ISO 3318
Standard	DIN 3110
Jaw position 1	15 °
Jaw position 2	15 °
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner