



Double open ended spanner, Jaw widths: 12X13mm



Order data

| | |
|--------------|---------------|
| Order number | 610100 12X13 |
| GTIN | 4018754017799 |
| Item class | 63A |

Description

Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 610600

Technical description

| | |
|----------------------|----------|
| Width across flats 1 | 12 mm |
| maximum jaw width b1 | 29 mm |
| maximum jaw height h | 6 mm |
| maximum jaw width b2 | 31 mm |
| Width across flats 2 | 13 mm |
| Width across flats | metric |
| Spanner length L | 170 mm |
| Standard | ISO 3318 |
| Standard | DIN 3110 |

| | |
|---|------------|
| Jaw position 1 | 15 degrees |
| Jaw position 2 | 15 degrees |
| non-sparking | no |
| both sides have the same width across flats | no |
| Type of product | Spanner |