



Double open ended spanner, inch, Type: 3



Order data

| | |
|--------------|---------------|
| Order number | 610120 3 |
| GTIN | 4018754019731 |
| Item class | 63A |

Description

Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Technical description

| | |
|---------------------------------|------------|
| maximum jaw width b2 | 23 mm |
| maximum jaw width b1 | 18 mm |
| maximum jaw height h | 4.5 mm |
| Width across flats | imperial |
| Width across flats ₂ | 3/8 in |
| Spanner length L | 140 mm |
| Width across flats ₁ | 5/16 in |
| Standard | ISO 3318 |
| Standard | DIN 3110 |
| Jaw position 1 | 15 degrees |
| Jaw position 2 | 15 degrees |

| | |
|---|---------|
| non-sparking | no |
| both sides have the same width across flats | no |
| Type of product | Spanner |