



Double open ended spanner, inch, Type: 19



Order data

Order number	610120 19
GTIN	4018754019847
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Width across flats $_1$: 25/32 in

Width across flats $_2$: 13/16 in

Spanner length L: 235 mm

maximum jaw width b1: 45 mm

maximum jaw width b2: 47 mm

maximum jaw height h: 7.3 mm

Technical description

maximum jaw height h	7.3 mm
maximum jaw width b1	45 mm
maximum jaw width b2	47 mm
Width across flats	imperial
Width across flats $_2$	13/16 in
Spanner length L	235 mm
Width across flats $_1$	25/32 in

Standard	ISO 3318
Standard	DIN 3110
Jaw position 1	15 °
Jaw position 2	15 °
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner