



Double open ended spanner, inch, Type: 5



Order data

Order number	610120 5
GTIN	4018754019748
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Technical description

maximum jaw height h	4.8 mm
maximum jaw width b1	23 mm
maximum jaw width b2	26 mm
Width across flats	imperial
Width across flats ₂	7/16 in
Spanner length L	155 mm
Width across flats ₁	3/8 in
Standard	ISO 3318
Standard	DIN 3110
Jaw position 1	15 degrees
Jaw position 2	15 degrees

non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner