



Double open ended spanner, Jaw widths: 5,5X7mm



Order data

Order number	610100 5,5X7
GTIN	4018754018147
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 610600

Technical description

maximum jaw height h	4 mm
Width across flats 2	7 mm
Width across flats 1	5.5 mm
maximum jaw width b1	15 mm
maximum jaw width b2	17 mm
Width across flats	metric
Spanner length L	120 mm
Standard	ISO 3318
Standard	DIN 3110

Jaw position 1	15 degrees
Jaw position 2	15 degrees
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner