



Double open ended spanner, inch, Type: 24



Order data

Order number	610120 24
GTIN	4018754019878
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Technical description

maximum jaw width b1	53 mm
maximum jaw height h	8.3 mm
maximum jaw width b2	55 mm
Width across flats	imperial
Width across flats ₂	1 in
Spanner length L	270 mm
Width across flats ₁	15/16 in
Standard	ISO 3318
Standard	DIN 3110
Jaw position 1	15 degrees
Jaw position 2	15 degrees

non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner