



## Double open ended spanner, inch, Type: 8



### Order data

Order number	610120 8
GTIN	4018754019762
Item class	63A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission.

#### Standard:

**DIN 3110 / ISO 3318**

#### Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

### Technical description

maximum jaw height h	5.3 mm
maximum jaw width b1	30 mm
maximum jaw width b2	32 mm
Width across flats	imperial
Width across flats <sub>2</sub>	9/16 in
Spanner length L	190 mm
Width across flats <sub>1</sub>	1/2 in
Standard	ISO 3318
Standard	DIN 3110
Jaw position 1	15 degrees
Jaw position 2	15 degrees

non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner