



## Double open ended spanner, Jaw widths: 4X5 mm



### Order data

Order number	610700 4X5
GTIN	4045197158819
Item class	61A

### Description

#### Version:

Drop forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance.

#### Standard:

**DIN 3110 / ISO 3318**

#### Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

Spanner length L: 100 mm

maximum jaw width b1: 13 mm

maximum jaw width b2: 14 mm

maximum jaw height h: 3 mm

### Technical description

Width across flats 1	4 mm
maximum jaw width b1	13 mm
maximum jaw height h	3 mm
maximum jaw width b2	14 mm
Width across flats 2	5 mm
Width across flats	metric
Spanner length L	100 mm
Norm	DIN 3110
Norm	ISO 3318

Jaw position 1	15 degrees
Jaw position 2	15 degrees
non-sparking	no
both sides have the same width across flats	no