



## Double open ended spanner, chrome-plated, Jaw widths: 7X8mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 610950 7X8    |
| GTIN         | 4045197441430 |
| Item class   | 62A           |

### Description

**Version:**

Drop-forged. With close tolerance jaw widths.  
With oval shaft.

**Standard:**

**DIN 3110 / ISO 3318**

**Material:**

Chrome vanadium steel, chrome-plated.

### Technical description

|                      |            |
|----------------------|------------|
| Width across flats 2 | 8 mm       |
| maximum jaw width b2 | 20 mm      |
| maximum jaw width b1 | 18 mm      |
| Width across flats 1 | 7 mm       |
| maximum jaw height h | 4 mm       |
| Width across flats   | metric     |
| Spanner length L     | 130 mm     |
| Standard             | DIN 3110   |
| Standard             | ISO 3318   |
| Jaw position 1       | 15 degrees |
| Jaw position 2       | 15 degrees |

|   |               |
|---|---------------|
| Surface                                     | chrome plated |
| Product name attribute                      | chrome-plated |
| non-sparking                                | no            |
| both sides have the same width across flats | no            |
| Type of product                             | Spanner       |