



Double open ended spanner, Jaw widths: 21X24 mm



Order data

Order number	610700 21X24
GTIN	4045197159052
Item class	61A

Description

Version:

Drop forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

Spanner length L: 250 mm

maximum jaw width b1: 47 mm

maximum jaw width b2: 53 mm

maximum jaw height h: 8 mm

Technical description

maximum jaw width b1	47 mm
maximum jaw width b2	53 mm
Width across flats 1	21 mm
maximum jaw height h	8 mm
Width across flats 2	24 mm
Width across flats	metric
Spanner length L	250 mm
Norm	DIN 3110
Norm	ISO 3318

Jaw position 1	15 degrees
Jaw position 2	15 degrees
non-sparking	no
both sides have the same width across flats	no