

**Double open ended spanner, phosphated, Jaw widths: 10X11mm****Order data**

Order number	610900 10X11
GTIN	4045197348623
Item class	62A

**Description****Version:**

Drop-forged. With close tolerance jaw widths.  
With oval shank.

**Standard:**

**DIN 3110 / ISO 3318**

**Material:**

Chrome vanadium steel, phosphated.

**Technical description**

maximum jaw height h	5 mm
maximum jaw width b2	27 mm
Width across flats 1	10 mm
maximum jaw width b1	24 mm
Width across flats 2	11 mm
Width across flats	metric
Spanner length L	151 mm
Standard	DIN 3110
Standard	ISO 3318
Jaw position 1	15 degrees
Jaw position 2	15 degrees

Surface	phosphated
Product name attribute	phosphated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner