



## Double open ended spanner, phosphated, Jaw widths: 24X26mm



### Order data

Order number	610900 24X26
GTIN	4045197384287
Item class	62A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.  
With oval shank.

#### Standard:

**DIN 3110 / ISO 3318**

#### Material:

Chrome vanadium steel, phosphated.

### Technical description

maximum jaw height h	9 mm
Width across flats 1	24 mm
maximum jaw width b1	54 mm
Width across flats 2	26 mm
maximum jaw width b2	58 mm
Width across flats	metric
Spanner length L	265 mm
Standard	DIN 3110
Standard	ISO 3318
Jaw position 1	15 degrees
Jaw position 2	15 degrees

Surface	phosphated
Product name attribute	phosphated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner