



## Open ended spanner set, Number of keys: 10



### Order data

Order number	610710 10
GTIN	4045197159168
Item class	61A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance.

#### Standard:

**DIN 3110 / ISO 3318**

#### Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

#### Supplied with:

1 each spanner No. 610700 / 610100 / 610900 / 610950 / 610120: Size 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×19; 20×22; 21×24; 27×30

### Technical description

Number of keys	10
Width across flats	metric
Jaw position 1	15 degrees
Jaw position 2	15 degrees

### Accessories

Plastic clip holder with closure flap for number of sockets  
11

---

611700 11