



## Open ended spanner set, Number of keys: 12



### Order data

Order number	610710 12
GTIN	4045197159175
Item class	61A

### Description

**Version:**

Drop-forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance.

**Standard:**

**DIN 3110 / ISO 3318**

**Material:**

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

**Supplied with:**

1 each spanner No. 610700 / 610100 / 610900 / 610950 / 610120: Size 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×19; 20×22; 21×23; 24×26; 27×32; 30×34

### Technical description

Number of keys	12
Width across flats	metric
Jaw position 1	15 degrees
Jaw position 2	15 degrees

### Accessories

Plastic clip holder for number of sockets 12

611500 12