

**Double open ended spanner, Jaw widths: 24X26 mm****Order data**

Order number	610700 24X26
GTIN	4045197159076
Item class	61A

Description**Version:**

Drop forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

Spanner length L: 270 mm

maximum jaw width b1: 54 mm

maximum jaw width b2: 58 mm

maximum jaw height h: 9 mm

Technical description

Width across flats 1	24 mm
maximum jaw width b1	54 mm
maximum jaw height h	9 mm
Width across flats 2	26 mm
maximum jaw width b2	58 mm
Width across flats	metric
Spanner length L	270 mm
Norm	DIN 3110
Norm	ISO 3318

Jaw position 1	15 degrees
Jaw position 2	15 degrees
non-sparking	no
both sides have the same width across flats	no