

**Double open ended spanner, phosphated, Jaw widths: 17X19mm****Order data**

Order number	610900 17X19
GTIN	4045197348647
Item class	62A

**Description****Version:**

Drop-forged. With close tolerance jaw widths.  
With oval shank.

**Standard:**

**DIN 3110 / ISO 3318**

**Material:**

Chrome vanadium steel, phosphated.

**Technical description**

Width across flats 1	17 mm
maximum jaw height h	7 mm
maximum jaw width b2	43 mm
maximum jaw width b1	40 mm
Width across flats 2	19 mm
Width across flats	metric
Spanner length L	220 mm
Standard	DIN 3110
Standard	ISO 3318
Jaw position 1	15 degrees
Jaw position 2	15 degrees

Surface	phosphated
Product name attribute	phosphated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner