

**Double open ended spanner, phosphated, Jaw widths: 11X13mm****Order data**

| | |
|--------------|---------------|
| Order number | 610900 11X13 |
| GTIN | 4045197384119 |
| Item class | 62A |

Description**Version:**

Drop-forged. With close tolerance jaw widths.
With oval shank.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome vanadium steel, phosphated.

Technical description

| | |
|----------------------|------------|
| maximum jaw width b2 | 31 mm |
| Width across flats 1 | 11 mm |
| Width across flats 2 | 13 mm |
| maximum jaw height h | 6 mm |
| maximum jaw width b1 | 29 mm |
| Width across flats | metric |
| Spanner length L | 171 mm |
| Standard | DIN 3110 |
| Standard | ISO 3318 |
| Jaw position 1 | 15 degrees |
| Jaw position 2 | 15 degrees |

| | |
|---|------------|
| Surface | phosphated |
| Product name attribute | phosphated |
| non-sparking | no |
| both sides have the same width across flats | no |
| Type of product | Spanner |