



## Double open ended spanner, chrome-plated, Jaw widths: 10X13mm



### Order data

Order number	610950 10X13
GTIN	4045197159236
Item class	62A

### Description

**Version:**

Drop-forged. With close tolerance jaw widths.  
With oval shaft.

**Standard:**

**DIN 3110 / ISO 3318**

**Material:**

Chrome vanadium steel, chrome-plated.

### Technical description

maximum jaw width b1	26 mm
Width across flats 2	13 mm
maximum jaw width b2	31 mm
Width across flats 1	10 mm
maximum jaw height h	6 mm
Width across flats	metric
Spanner length L	171 mm
Standard	DIN 3110
Standard	ISO 3318
Jaw position 1	15 degrees
Jaw position 2	15 degrees

Surface	chrome plated
Product name attribute	chrome-plated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner