



Double open ended spanner, Jaw widths: 27X30 mm



Order data

Order number	610700 27X30
GTIN	4045197159090
Item class	61A

Description

Version:

Drop forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

Spanner length L: 300 mm

maximum jaw width b1: 60 mm

maximum jaw width b2: 66 mm

maximum jaw height h: 10 mm

Technical description

maximum jaw width b2	66 mm
maximum jaw height h	10 mm
Width across flats 2	30 mm
Width across flats 1	27 mm
maximum jaw width b1	60 mm
Width across flats	metric
Spanner length L	300 mm
Norm	DIN 3110
Norm	ISO 3318

Jaw position 1	15 degrees
Jaw position 2	15 degrees
non-sparking	no
both sides have the same width across flats	no