



Double open ended spanner, chrome-plated, Jaw widths: 17X19mm



Order data

Order number	610950 17X19
GTIN	4045197159304
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw widths.
With oval shaft.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Spanner length L: 220 mm

maximum jaw width b1: 40 mm

maximum jaw width b2: 43 mm

maximum jaw height h: 7 mm

Technical description

Width across flats 1	17 mm
maximum jaw height h	7 mm
maximum jaw width b2	43 mm
Width across flats 2	19 mm
maximum jaw width b1	40 mm
Width across flats	metric
Spanner length L	220 mm
Standard	DIN 3110
Standard	ISO 3318

Jaw position 1	15 °
Jaw position 2	15 °
Surface	chrome plated
Product name attribute	chrome-plated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner