

**Double open ended spanner, phosphated, Jaw widths: 19X22mm****Order data**

Order number	610900 19X22
GTIN	4045197384225
Item class	62A

Description**Version:**

Drop-forged. With close tolerance jaw widths.
With oval shank.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome vanadium steel, phosphated.

Technical description

Width across flats 1	19 mm
maximum jaw height h	8 mm
maximum jaw width b2	49 mm
maximum jaw width b1	44 mm
Width across flats 2	22 mm
Width across flats	metric
Spanner length L	235 mm
Standard	DIN 3110
Standard	ISO 3318
Jaw position 1	15 degrees
Jaw position 2	15 degrees

Surface	phosphated
Product name attribute	phosphated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner