



Working area lamp Planonlight LED Black Series, Power consumption: 10W



Order data

Order number	081353 10
GTIN	2050001919397
Item class	04E

Description

Version:

Planonlight LED-light **black series** is the most intense, **most dense** and **most compact** of the Planonlight work lights. Add-on variant with flexible fastening options for the most demanding industrial applications.

- **Very high illumination intensity with 157 Lumen/Watt LEDs.**
- **Absolutely maintenance-free (with a long working life of 50,000 h).**
- **Very compact design makes it ideal for retrofitting and for use in very intricate machines.**
- **Very wide range of variants, with 8 different models (built-in versions on request).**
- **Flexible attachment: Flush fitted in-built or with suitable, adjustable attachment 081381 for 45° surface mounting.**
- **Improved and proven sealing principle with IP68 and IP69K (leak-free against emulsion).**

Note:

Operating voltage 24 V DC – connection directly to the mains (230 V/50 Hz) will damage the lamp beyond repair! Use transformer No. 081375 to connect to the mains.

Technical description

Weight	500 g
--------	-------

Illumination	1300 lm
Power consumption	10 W
Beam dispersion angle fixed	120 degrees
Bulb	LED module
Temperature range	-20 - 55 °C
Overall height	20 mm
Colour temperature	6500 K
Power supply	Mains operated
Overall width	65 mm
Overall length	168.5 mm
ATEX zone	no
Manufacturer's designation	10487
Type of product	Machine lamp

Accessories

Transformer for PLANONLIGHT LED 24 V / 100 W	081375
Bracket for Black series 45°	081381