

**LOCTITE****Thread sealant, 50 ml, Manufacturer ID: 511\_DIER**

---

## Order data

Order number	083321 511_DIER
GTIN	4058093009192
Item class	04L

---

## Description

**Version:**

These sealants replace hemp, sealing tapes, and pastes, they are resistant to gases, liquids, air, water, oils, hydrocarbons and many chemical products. **Complete surface contact** ensures a **100% seal**. Unscrewing, or correction of position during assembly can be performed using conventional tools at any time before the sealant hardens. No sealant residues to block filters and valves.

**Application:**

Suitable for metal threads up to M80 / R3.

**Note:**

Before applying sealant, clean the threads with general-purpose cleaner No. 083391/3392.

Labelling of hazardous substances: GHS07 caution

Manufacturer's designation: 511

Colour of sealant: white

minimum break-away torque: 6 N·m

Temperature range: -55 - 150 °C

for thread size M to: M80

for imperial thread size: 3 inch

---

## Technical description

Content of stick	g
Top-up fluid	50 ml
Product name attribute	50 ml
Type of product	

