



Smooth rolling roller, convex, Roll Ø: 15mm



Order data

Order number	291440 15
GTIN	4030741009327
Item class	29H

Description

Version:

Turned and polished ($R_z = 4 \mu\text{m}$).
Convex HSS smooth rolling rollers – type RRE.

Advantage:

- **Improved surface quality.**
- **Hardening of surfaces.**
- **Reduction of process time.**

Application:

For smooth rolling of cylindrical workpieces.

Suitable for:

Knurl forming tool: No. 290000; 290001

Technical description

Roller hole Ø	4 mm
Roll Ø	15 mm
Roller width	4 mm

Tool material	HSS
Roughness value	4 μm
Shape	convex
Type	RRE
Type of product	Smooth rolling tool