



## Smooth rolling roller, convex, Roll Ø: 10mm



### Order data

Order number	291445 10
GTIN	4030741390135
Item class	29H

### Description

#### Version:

Ground and polished ( $R_z = 1 \mu\text{m}$ ).  
Convex HSS smooth rolling rollers – type RRE.

#### Advantage:

- **Improved surface quality.**
- **Hardening of surfaces.**
- **Reduction of process time.**

#### Application:

For smooth rolling of cylindrical workpieces.

#### Suitable for:

Knurl forming tool: No. 290000; 290001

### Technical description

Roller hole Ø	4 mm
Roll Ø	10 mm
Roller width	4 mm

Tool material	HSS
Roughness value	1 $\mu\text{m}$
Shape	convex
Type	RRE
Type of product	Smooth rolling tool