

**Office racking basic rack, Depth 300 mm, Height /storage shelf width:  
2300/1000mm****Order data**

Order number	990590 2300/1000
GTIN	4004514219930
Item class	96P

**Description****Version:**

T-profile frame fronts and storage shelves without any holes.

Stiffening by cross-strut. Stop strips prevent files or the documents being pushed through. The top shelf has no stop strip.

**Maximum load capacity: 85 kg per storage shelf.**

Rack depth 300 mm: at 2300 mm height, takes up to 96 files per bay.

**Description:**

Assembled size:

Basic rack: Nominal length + 60 mm

Extension rack: Nominal length +6 mm

Overall depth of the rack: Nominal depth + 36 mm

Unsupported length: max. 600 mm

**Note:**

- **To ensure the stability of the racking, measures to prevent tipping are necessary where the height to depth ratio is greater than 5:1.**
- **Floor and wall fastenings not supplied.**

**Technical description**

Height	2300 mm
Assembled size basic rack width	1060 mm
Width	1000 mm
Number of shelves	7
Depth	300 mm
Shelf thickness	25 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanised
Product name attribute	Depth 300 mm
Type of product	File racking

---

## Accessories

Clamping base	990852
---------------	--------