

Office racking extension rack, Depth 300 mm, Height /storage shelf width: 2000/1000mm



Order data

Order number	990591 2000/1000
GTIN	4004514219909
Item class	96P

Description

Version:

T-profile frame fronts and storage shelves without any holes.

Stiffening by cross-strut. Stop strips prevent files or the documents being pushed through. The top shelf has no stop strip.

Maximum load capacity: 85 kg per storage shelf.

Rack depth 300 mm: at 2300 mm height, takes up to 96 files per bay.

Description:

Assembled size:

Basic rack: Nominal length + 60 mm

Extension rack: Nominal length +6 mm

Overall depth of the rack: Nominal depth + 36 mm

Unsupported length: max. 600 mm

Note:

- To ensure the stability of the racking, measures to prevent tipping are necessary where the height to depth ratio is greater than 5:1.
- Floor and wall fastenings not supplied.

Technical description

Depth	300 mm
Height	2000 mm
Assembled size add-on rack width	1006 mm
Width	1000 mm
Number of shelves	6
Shelf thickness	25 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanised
Product name attribute	Depth 300 mm
Type of product	File racking

Accessories

Clamping base	990852
---------------	--------