

## Office racking basic rack, Depth 600 mm, Height /storage shelf width: 2000/1000mm



### Order data

Order number	990595 2000/1000
GTIN	4004514220080
Item class	96P

### Description

#### Version:

T-profile frame fronts and storage shelves without any holes.

Stiffening by lengthways bars. Centre stop strip prevents files or the documents being pushed through. The top shelf has no centre stop strip.

#### Maximum load capacity: 150 kg per storage shelf.

Rack depth 600 mm: Can be accessed from both sides. At 2300 mm height, takes up to 192 files per bay.

#### Description:

Assembled size:

Basic rack: Nominal length + 60 mm

Extension rack: Nominal length +6 mm

Overall depth of the rack: Nominal depth + 36 mm

Unsupported length: max. 600 mm

#### Note:

- To ensure the stability of the racking, measures to prevent tipping are necessary where the height to depth ratio is greater than 5:1.
- Floor and wall fastenings not supplied.

### Technical description

Width	1000 mm
-------	---------

Number of shelves	6
Height	2000 mm
Assembled size basic rack width	1060 mm
Depth	600 mm
Shelf thickness	25 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanised
Product name attribute	Depth 600 mm
Type of product	File racking

---

## Accessories

Clamping base	990852
---------------	--------