



## Double open ended spanner, Jaw widths: 32X36 mm



### Order data

Order number	610700 32X36
GTIN	4045197159137
Item class	61A

### Description

#### Version:

Drop forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance.

#### Standard:

**DIN 3110 / ISO 3318**

#### Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

Spanner length L: 325 mm

maximum jaw width b1: 70 mm

maximum jaw width b2: 80 mm

maximum jaw height h: 10 mm

### Technical description

maximum jaw height h	10 mm
maximum jaw width b1	70 mm
Width across flats 2	36 mm
Width across flats 1	32 mm
maximum jaw width b2	80 mm
Width across flats	metric
Spanner length L	325 mm
Norm	DIN 3110
Norm	ISO 3318

Jaw position 1	15 degrees
Jaw position 2	15 degrees
non-sparking	no
both sides have the same width across flats	no