



Snipe-nose pliers, straight Insulated to VDE, with securing eye, Overall length: 200mm



Order data

Order number	706030 200
GTIN	4003773081449
Item class	73F

Description

Version:

Pliers with a securing eye for fitting a safety harness. Securing eye, welded to the grip, dynamic load capacity up to 3 m drop height.

Insulated to DIN EN IEC 60900 / VDE 06082-201 for working at voltages up to 1000 V.

Application:

For use in building construction, underground construction, building maintenance, on industrial structural work, roofing work, in exhibition stand construction, etc.

Material:

Chrome vanadium electro-steel, drop forged.

Note:

Other versions and sizes available on request.

Technical description

Jaw length	70 mm
overall length	200 mm
Material	Chrome vanadium electro-steel
Type of product	Multi-function pliers

Accessories

CarabinerSTEEL D TRI	098195
ConnectorSpiral retainer cord Type T2T	098245 T2T
CarabinerDOUBLE TRI	098194
CarabinerOVALSTEEL SC Type	098196
ConnectorBungee Load capacity 15,9 kg	098240 15,9