



## Diagonal side cutter Insulated to VDE, with securing eye, Overall length: 160mm



### Order data

Order number	706040 160
GTIN	4003773081463
Item class	73F

### Description

#### Version:

Pliers with a securing eye for fitting a safety harness. Securing eye, welded to the grip, dynamic load capacity up to 3 m drop height.

**Insulated up to 1000 Volts to DIN EN 60900 / VDE 0682-201.**

#### Application:

For use in building construction, underground construction, building maintenance, on industrial structural work, roofing work, in exhibition stand construction, etc.

#### Material:

Chrome vanadium electro-steel, drop forged.

#### Note:

Other versions and sizes available on request.

Cutting capacity soft wire up to Ø: 4 mm

Cutting capacity hard wire up to Ø: 2 mm

### Technical description

overall length	160 mm
Cutting capacity soft wire up to Ø	4 mm
Cutting capacity hard wire up to Ø	2 mm
Type of product	Cutting pliers

## Accessories

Connector Spiral retainer cord Type C2L	098245 C2L
Connector Spiral retainer cord Type T2T	098245 T2T
Carabiner STEEL D TRI	098195
Carabiner DOUBLE TRI	098194
Attachment point Type 1	098230 1
Connector Spiral retainer cord Type H2H	098245 H2H
Attachment point Type 2	098230 2
Wrist strap Type 2	098250 2
Connector Bungee Load capacity 15,9 kg	098240 15,9
Connector Bungee Load capacity 4,5 kg	098240 4,5
Carabiner OVALSTEEL SC	098196
Wrist strap Type 1	098250 1