

**Double open ended spanner, chrome-plated, Jaw widths: 13X15mm****Order data**

Order number	610950 13X15
GTIN	4045197159250
Item class	62A

Description**Version:**

Drop-forged. With close tolerance jaw widths.
With oval shaft.

Standard:

DIN 3110 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Technical description

Width across flats 1	13 mm
maximum jaw width b1	33 mm
maximum jaw width b2	35 mm
Width across flats 2	15 mm
maximum jaw height h	6 mm
Width across flats	metric
Spanner length L	186 mm
Standard	DIN 3110
Standard	ISO 3318
Jaw position 1	15 degrees
Jaw position 2	15 degrees

Surface	chrome plated
Product name attribute	chrome-plated
non-sparking	no
both sides have the same width across flats	no
Type of product	Spanner