

Koken
Extension, 1/4 inch "Wobble-Fix", overall length: 50mm


Order data

Order number	632525 50
GTIN	4991644021024
Item class	63R

Description

Version:

Material selection and special forging process guarantee optimal external square drives to DIN 3120 A 6.3 with sprung ball, internal square drives to DIN 3120.

Two-stage extension. The wobble type extension clicks into place and allows up to 15° of movement.

"Blind" interlocking possible due to bevelled edges on male and female coupling.

Standard:

DIN 3123-B 6,3

Material:

Chrome vanadium steel, chrome-plated.

Suitable for:

Manual use.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 632519

Technical description

overall length	50 mm
Square drive	1/4 in
Square with Wobble-Fix	with angle of inclination
Type of product	Extension

